

High Accuracy Bench-top Spectrophotometer



# CS-826

## Product Features

- Automatic calibration
- High stability UV light source, providing stable fluorescence measurement result
- Excellent repeatability when measuring on black samples
- Excellent consistency with other competing products made in United States, Japan, and Europe
- Excellent long-term repeatability, even after rapid changes in the environment can still guarantee excellent repeatability
- It has two lamps: pulsed xenon and LED
- 24 kinds of illuminants and more than 40 measurement indices
- Temperature and humidity compensation function
- Ten-inch screen, Android operate system
- Dual optical paths spectrum analysis technology
- Support SCI+SCE simultaneous rapid measurement

## Technical Data

Name	Specifications
Illumination/ Viewing System	Reflectance: d/8(Diffused illumination, 8 degree viewing) Simultaneous measurement of SCI/SCE, conform to CIE No.15, GB/T 3978, GB 2893, GB/T 18833, ISO7724/1, DIN5033 Teil7, JIS Z8722 condition C, ASTM E1164,ASTM-D1003-07 Transmittance d/0(Diffused illumination, 0 degree viewing )
Sensor	Silicon Photodiode Array
Grating Method	Concave Grating
Sphere Diameter	152mm
Wavelength Range	360nm-780nm
Wavelength Pitch	10nm
Half Band Width	1nm
Reflectance Range Resolution	0-200%,0.01%
Light Source	Pulse Xenon Lamp and LED
UV Measurement	Include UV, 400nm cut, 420nm cut, 460nm cut
Measurement Time	SCI/SCE < 2s; SCI+SCE < 4s
Measurement Aperture	Reflectance: XLAV Φ25.4mm/Φ30mm, LAV Φ15mm/18mm,MAV Φ8mm/Φ11mm,SAV Φ3mm/Φ6mm Transmittance:Φ17mm/Φ25mm (Auto aperture size recognition)
Transmittance Sample Size	No limit on sample width and height, thickness ≤50mm
Long Term Repeatability	XLAV Chromaticity value: Standard deviation within ΔE*ab 0.015 (20℃±10℃ arbitrary temperature change, white tile is measured every hour within 24 hours)
Repeatability	XLAV Spectrum Reflectance/Transmittance: standard deviation within 0.1%;XLAV Chromaticity value: Standard deviation within ΔE*ab 0.01 (max 0.02) * When a white tile is measured 30 x at 10-second intervals after white calibration
Inter-Instrument Agreement	XLAV ΔE*ab 0.1 (BCRA Series II, Average measurement of 12 tiles, at 23℃)
Observer	2° and 10°
Illuminants	A,C,D50,D55,D65,D75,F1,F2,F3,F4,F5,F6,F7,F8,F9,F10,F11,F12,CWF,U30,DLF,NBF,TL83,TL84
Language	English, Russian, Spanish, Portuguese, Japanese, Thai, Korean, German, French, Polish, Chinese (simple and traditional),
Display	Reflectance and Transmittance graph/value, color value, color difference values, pass/fail, color simulation, color assessment, haze, liquidchromaticity values, color tendency
Color Spaces	L*a*b,L*C*h,Hunter Lab,Yxy,XYZ
Other Indices	WI(ASTM E313-00,ASTM E313-73,CIE/ISO, AATCC, Hunter, Taube Berger, Stensby) YI(ASTM D1925,ASTM E313-00,ASTM E313-73),Tint(ASTM E313-00),Metamerism index milm, stain fastness,color fastness, ISO brightness, R457, A density, T density, E density, M Density, APHA/Pt-Co/Hazen, Gardner, Saybolt, ASTM color, Haze, Total Transmittance, Opacity, Color Strength
Color Difference	ΔE*ab, ΔE*CH, ΔE*uv, ΔE*cmc, ΔE*94, ΔE*00, ΔE*ab(hunter),555 shade sort
Storage Memory	8GB
Screen Size	10 Inches Touch Screen
Operate System	Android
Power Adaptor	DC stabilized power supply
Operate Temperature	5-40℃ (40-104F), relative humidity 80% (at 35℃) no condensation
Storage Temperature	-20-45℃ (-4-113F), relative humidity 80% (at 35℃) no condensation
Accessories	Power Adaptor, USB Cable, fixture for transmittance, U disk (PC software), Black Calibration Cavity, White and Green Calibration Tile, Reflectance Test Support,30mm,18mm,11mm and 6mm apertures, reflectance sample fixture, Glass Cell 40x10mm,reflectance fixture
Optional Accessories	Heating Fixture for Transmittance, Vertical Support and Pneumatic ram for downward measurement, Reflectance fixture for small size sample, Reflectance Glass Cell Support, Corrosion-Resistant Protective Plate (non-removable), Sample Holder for Fiber, Film Fixture, Transmittance Fixture for Small Aperture, Trolley Case, European Standard Plug, American Standard Plug
Other Function	RS-232、USB、USB-B
Interface	1. Camera to view measurement area;2. Support horizontal, vertical and downward measurement method (need optional accessories to support for downward measurement);3. Auto humidity and temperature compensation function.